

## Han PushPull RJ45 housing with gasket



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 002 0321
Specification	Han PushPull RJ45 housing with gasket
HARTING eCatalogue	<a href="https://harting.com/09350020321">https://harting.com/09350020321</a>

### Identification

Category	Connectors
Series	Han® PushPull (V14)
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With integrated seal

### Version

Locking type	PushPull
--------------	----------

### Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

## Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	IEC 61076-3-117
PROFINET	Yes

## Commercial data

Packaging size	1
Net weight	3.38 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140053618
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466