

Han 6Ex UL-HBM-SL



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 36 506 1301 |
| Specification | Han 6Ex UL-HBM-SL |
| HARTING eCatalogue | https://harting.com/09365061301 |

Identification

| | |
|--------------------------|--------------------------|
| Category | Hoods / Housings |
| Series of hoods/housings | Han® Ex |
| Type of hood/housing | Bulkhead mounted housing |

Version

| | |
|----------------------|--|
| Size | 6 B |
| Locking type | Single locking lever |
| Field of application | Connectors for explosion hazardous environments |
| Details | for US purposes only |
| Details | ATTENTION! Only to be used with Han® Ex inserts! |

Technical characteristics

| | |
|--|--|
| Tightening torque | 1 Nm Fixing screws M4 |
| Limiting temperature | -20 ... +85 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Ambient temperature | -20 ... +40 °C Up to +70 °C in T4 |
| Degree of protection acc. to IEC 60529 | IP65 With cable gland |

Material properties

| | |
|-------------------------|---------------------|
| Material (hood/housing) | Zinc die-cast |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 5015 (sky blue) |
| Material (seal) | NBR |

Material properties

| | |
|--------------------------------------|-----------------|
| Material (locking) | Stainless steel |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead Nickel |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 202 g |
| Country of origin | China |
| European customs tariff number | 85389099 |
| GTIN | 5713140181540 |
| eCl@ss | 27440202 Shell for industrial connectors |
| ETIM | EC000437 |
| UNSPSC 24.0 | 39121466 |