

Han 6HPR Cover Toggle Locking




Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 40 006 5401 |
| Specification | Han 6HPR Cover Toggle Locking |
| HARTING eCatalogue | https://harting.com/09400065401 |

Identification

| | |
|------------------------------|---|
| Category | Accessories |
| Series of hoods/housings | Han® HPR |
| Type of accessory | Protection cover |
| Description of the accessory | for bulkhead mounted housings for surface mounted housings |

Version

| | |
|--------------|----------------|
| Size | 6 B |
| Locking type | Toggle locking |

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65 IP68 |
| Type rating acc. to UL 50 / UL 50E | 4 4X 12 |

Material properties

| | |
|-------------------------|---|
| Material (hood/housing) | Aluminium die-cast Corrosion resistant |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material (locking) | Stainless steel |
| RoHS | compliant |

Material properties

| | |
|--------------------------------------|----------------------------|
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead Nickel |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R1 (HL 1-3) R7 (HL 1-3) |

Specifications and approvals

| | |
|-----------|--|
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | DNV GL |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 14 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140057340 |
| eCl@ss | 27440208 Cap for industrial connectors |
| ETIM | EC002314 |
| UNSPSC 24.0 | 39121467 |