

## RJ45 MF RJ45 plug Cat6A, 8p IDC angled



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 151 1571
Specification	RJ45 MF RJ45 plug Cat6A, 8p IDC angled
HARTING eCatalogue	<a href="https://harting.com/09451511571">https://harting.com/09451511571</a>

### Identification

Category	Connectors
Series	HARTING RJ Industrial® RJ45
Element	Cable connector
Specification	PROFINET Multi Feature RJ45 90° angled
Features	Suitable for all PoE versions

### Version

Termination method	IDC insulation displacement termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8

### Technical characteristics

Conductor cross-section	0.12 ... 0.32 mm <sup>2</sup> Stranded 0.12 ... 0.32 mm <sup>2</sup> Solid
Conductor cross-section [AWG]	AWG 26/7 ... AWG 22/7 Stranded AWG 26/1 ... AWG 22/1 Solid
Wire outer diameter	0.8 ... 1.6 mm
Rated current	1.76 A
Rated voltage	50 V AC 60 V DC
Transmission characteristics	Cat. 6 <sub>A</sub> Class E <sub>A</sub> up to 500 MHz



**Pushing Performance**  
 Since 1945

## Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Insulation resistance	$> 5 \times 10^9 \Omega$
Contact resistance	$\leq 20 \text{ m}\Omega$
Contact resistance, shielding	$\leq 100 \text{ m}\Omega$
Limiting temperature	-40 ... +85 °C
Relative humidity	95 % Non-condensing (operation)
Insertion force	$\leq 25 \text{ N}$
Withdrawal force	$\leq 25 \text{ N}$
Mating cycles	$\geq 750$
Degree of protection acc. to IEC 60529	IP20
Cable diameter	4.5 ... 9 mm
Test voltage $U_{DC}$	1 kV (contact-contact)
	1.5 kV (contact-ground)
Vibration resistance	10-500 Hz, 0.35 mm / 50 m/s <sup>2</sup> , 2h/axis
	5.72 m/s <sup>2</sup> acc. to IEC 61373 Category 1 Class B
Shock resistance	50 g / 30 ms, 3 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

## Material properties

Material (insert)	Polycarbonate (PC)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
	Sn over Ni Termination side
Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Colour (hood/housing)	silver
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	IEC 60603-7 Mating face
	ISO/IEC 11801
	EN 50173-1
UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079
Approvals	DNV GL
PROFINET	Yes

## Commercial data

Packaging size	1
Net weight	34.37 g
Country of origin	Latvia
European customs tariff number	85366990
GTIN	5713140224346
eCl@ss	27440114 Rectangular connector (for field assembly)
ETIM	EC002636
UNSPSC 24.0	39121408