

## ix Industrial 10C-12 jack AV (T&R400)




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 283 3500
Specification	ix Industrial 10C-12 jack AV (T&R400)
HARTING eCatalogue	<a href="https://harting.com/09452833500">https://harting.com/09452833500</a>

### Identification

Category	Connectors
Series	HARTING ix Industrial®
Identification	Data
Element	PCB connector
Specification	Angled

### Version

Termination method	Solder termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
further contacts	+ 2x GND
Coding	Type C
Pack contents	On a reel

### Technical characteristics

Rated current	1.5 A 3 A
Rated current	1.5 A per contact 3 A per contact when used with 4 contacts (1,2,6,7)
Rated voltage	50 V AC 60 V DC
Transmission characteristics	Cat. 6A Class EA up to 500 MHz

## Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Insulation resistance	>500 MΩ
Contact resistance	≤30 mΩ
Shielding resistance	≤100 mΩ
Limiting temperature	-40 ... +85 °C
Storage temperature	-30 ... +60 °C
Relative humidity	95 % Non-condensing (operation) 95 % Non-condensing (storage/transport)
Insertion force	≤25 N
Withdrawal force	≤25 N
Mating cycles	≥5,000
Degree of protection acc. to IEC 60529	IP20
Test voltage $U_{DC}$	0.5 kV (contact-contact) 2.25 kV (contact-shielding)
Retention force	≥80 N locking
Moisture Sensitivity Level (MSL)	1 acc. to ECA/IPC/JEDEC J-STD-020D
Process Sensitivity Level (PSL)	R0 acc. to ECA/IPC/JEDEC J-STD-020D

## Material properties

Material (insert)	Liquid crystal polymer (LCP)
Colour (insert)	Grey
Material (shielding)	Stainless steel Sn ≥ 1 µm over Ni ≥ 0.2 µm Mating side (shielding)
Material (contacts)	Copper alloy
Surface (contacts)	Au ≥ 0.2 µm over Ni ≥ 2 µm Mating side Au ≥ 0.03 µm over Ni ≥ 2 µm Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

## Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	no requirements (flammable mass < 10g)


## Specifications and approvals

Specifications	IEC 61076-3-124 EN 45545-2
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079

## Commercial data

Packaging size	400
Net weight	3.04 g
Country of origin	Japan
European customs tariff number	85366930
GTIN	5713140324862
eCl@ss	27460201 PCB connector (board connector)
ETIM	EC002637
UNSPSC 24.0	39121415

## Contact configuration



<b>ix Industrial</b>	10/100 Mbit/s	1/10 Gbit/s	TIA	
			568 A	568 B
1	TX+	BI_DA+	White/Green	White/Orange
2	TX-	BI_DA-	Green	Orange
3	N.C	N.C	N.C	N.C
4	N.C	BI_DC+	Blue	Blue
5	N.C	BI_DC-	White/Blue	White/Blue
6	RX+	BI_DB+	White/Orange	White/Green
7	RX-	BI_DB-	Orange	Green
8	N.C	N.C	N.C	N.C
9	N.C	BI_DD+	White/Brown	White/Brown
10	N.C	BI_DD-	Brown	Brown

#### Environmental specifications

Rapid change of temperature (IEC 60512-11d)	10 cycles between -55°C and 85°C with 30 minutes dwell at temp. extremes and 2 to 3 minutes transition between temperatures
Dry heat (IEC 60512-11i)	+85°C, 500 h
Damp heat, steady state (IEC 60512-11-3)	40°C; relative humidity 93%; 500 h (Test 11c)
Damp heat, cycles (IEC 60068-2-38)	25°C to 65°C; cold sub-cycle: -10°C; relative humidity 93%; 10 cycles, 1 cycle/24h
Cold (IEC 60512-11j)	-55°C, 240h
Flow mixed gas test (IEC 60068-2-60)	4 d, Method 4 (mated and unmated)
Corrosion salt mist	Exposed at 5% salt water, 35°C, 48h (unmated); no heavy corrosion of contacts
Vibration, sinusoidal (IEC 60512-test 6d)	10 to 500 Hz; 0.35 mm, 50 m/s <sup>2</sup> , 2h / 3 axis; no contact disturbances $\geq 1\mu\text{s}$
Mechanical shock (IEC 60512-test 6d)	half-sine shock 300 m/s <sup>2</sup> , 11 ms 3 shocks / both directions / 3 axis - totally 18 shocks no contact disturbances $\geq 1\mu\text{s}$
Fretting Corrosion	490 m/s <sup>2</sup> , 30 times/min at 1000 times no contact disturbances $\geq 1\mu\text{s}$
Wrenching Strength	Applying 25 times / 30N for 1s / in 2 axis on tip of plug case in mated condition no damage, no cracks or looseness of parts