

PP-V4-CA-USB3A-PP/IP20-P-P-STR-5.0



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 45 445 2915 |
| Specification | PP-V4-CA-USB3A-PP/IP20-P-P-STR-5.0 |
| HARTING eCatalogue | https://harting.com/09454452915 |

Identification

| | |
|---------------|---|
| Category | System cabling |
| Series | HARTING PushPull (V4) |
| Element | Cable assemblies |
| Specification | Pre-assembled on both sides |
| Connector 1 | HARTING PushPull (V4) USB 3.0 Type A |
| Connector 2 | IP20 USB 3.0 Type A |
| Type of cable | Copper cable (round) |

Version

| | |
|-----------------|---|
| Cable length | 5 m |
| Number of cores | 8 |
| Core structure | 4x AWG 26/7 2x AWG 28/7 2x AWG 22/7 |
| Shielding | Shielded |

Technical characteristics

| | |
|-----------------------|---------------------------|
| Rated current | 1.5 A |
| Rated voltage | 30 V DC |
| Data rate | 5 Gbit/s |
| Insulation resistance | $>10^8 \Omega$ |
| Contact resistance | $\leq 30 \text{ m}\Omega$ |

Technical characteristics

| | |
|--|---|
| Limiting temperature | -40 ... +85 °C |
| Insertion force | ≤35 N |
| Withdrawal force | ≥15 N |
| Mating cycles | ≥750 |
| Degree of protection acc. to IEC 60529 | IP65 IP67 |
| Cable diameter | 6.2 mm |
| Test voltage $U_{r.m.s.}$ | 0.5 kV (contact-contact) 0.5 kV (contact-ground) |
| Impedance | 90 Ω ±15 % |

Material properties

| | |
|---|---|
| Material (insert) | Liquid crystal polymer (LCP) |
| Material (contacts) | Copper alloy |
| Surface (contacts) | Sn over Ni Termination side Au over Ni Mating side |
| Material (cable) | PVC |
| Colour (cable) | Black |
| Material (overmoulding) | Polyamide (PA) |
| Colour (overmoulding) | Black |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Not contained |

Specifications and approvals

| | |
|----------------|--------------------------------|
| Specifications | IEC 61076-3-106 Variant 4 (V4) |
|----------------|--------------------------------|

Commercial data

| | |
|----------------|-----------|
| Packaging size | 1 |
| Net weight | 297.145 g |

Commercial data

| | |
|--------------------------------|--|
| Country of origin | Malaysia |
| European customs tariff number | 85444290 |
| GTIN | 5713140262812 |
| eCl@ss | 27060390 Ready-made data cable (unspecified) |
| ETIM | EC002599 |
| UNSPSC 24.0 | 26121600 |