

HAR PROFINET Typ A 4xAWG22/1 PVC 500m




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 600 0110
Specification	HAR PROFINET Typ A 4xAWG22/1 PVC 500m
HARTING eCatalogue	https://harting.com/09456000110

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)
Description of the cable	Flame retardant Largely oil resistant Sunlight resistant
Printing on cable	HARTING INDUSTRIAL ETHERNET STANDARD CABLE CAT 5 PLUS * 22AWG (SHIELDED) (UL) E333432 VERIFIED CAT 5E CMG 75°C or PLTC or AWM 21694 600V FT4 SUN RES * 094560001000100 "Metermarkierung" "Jahr/Auftragsnummer""HARTING-LOGO"
Features	Suitable for permanent installation

Version

Cable length	500 m
Number of cores	4
Core structure	4x AWG 22/1

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +75 °C unmoved -20 ... +60 °C moved
Cable diameter	6.3 ... 6.7 mm



Pushing Performance
 Since 1945

Technical characteristics

Minimum bending radius	7.5x Cable diameter (repeated bending) 3x Cable diameter (singular bending)
Tensile strength	≤150 N
Test voltage $U_{r.m.s.}$	2 kV Wire / wire / shielding
Coupling attenuation @ 20 °C / 10 MHz	10 mΩ/m
Conductor resistance @ 20 °C	≤115 Ω/km
Insulation resistance @ 20 °C	≥500 MΩ x km
Signal run time @ 20 °C	≤5.3 ns/m
Impedance @ 100 MHz	100 Ω ±5 %

Material properties

Material (cable)	PVC
Colour (cable)	Green
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	ISO/IEC 11801
	EN 50173
	IEC 24702
	EN 50173-3
	EN 50288-2-1
	IEC 61156-5
	IEC 60332-1-2 Flame retardancy
UL / CSA	UL 1581
	UN/ECE-R 118 fire protection for rolling stock
	UL 444 DUZX.E333432
	CSA-C22.2 No. 214 DUZX7.E333432
PROFINET	Yes

Commercial data

Packaging size	1
----------------	---



Pushing Performance
Since 1945

Commercial data

Net weight	4 g
Net weight	66 g/m
Country of origin	Germany
European customs tariff number	85442000
GTIN	5713140061781
eCl@ss	27061801 Data and communication cable (copper)
ETIM	EC003249
UNSPSC 24.0	26121609