

Ha-Vis EtherRail 4xAWG22/7 bk CAT5 10m




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 600 0168
Specification	Ha-Vis EtherRail 4xAWG22/7 bk CAT5 10m
HARTING eCatalogue	https://harting.com/09456000168

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)
Description of the cable	for railway applications

Version

Cable length	10 m
Number of cores	4
Core structure	4x AWG 22/7

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
Limiting temperature	-25 ... +70 °C moved
	-40 ... +85 °C unmoved
Cable diameter	6.6 mm $\pm$ 0.2 mm
Minimum bending radius	6x Cable diameter
Test voltage $U_{r.m.s.}$	1 kV Wire / wire / shielding
Coupling attenuation @ 20 °C / 10 MHz	8 m Ω /m
Conductor resistance @ 20 °C	$\leq$ 54.4 Ω /km
Insulation resistance @ 20 °C	$\geq$ 5,000 M Ω x km
Signal run time @ 20 °C	$\leq$ 4.4 ns/m



Pushing Performance
Since 1945

Technical characteristics

Impedance @ 100 MHz	100 Ω $\pm$ 5 %
---------------------	------------------------

Material properties

Material (cable)	Polyolefin copolymer electron beam crosslinked Comp 752
Colour (cable)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	EN 45545-2 Fire protection on railway vehicles
	EN 50264-1 Fire protection on railway vehicles
	EN 50306-1 Fire protection on railway vehicles
	NFPA 130 Fire protection on railway vehicles
	UN/ECE-R 118 fire protection for rolling stock
	EN 50306-4 Resistance to ozone
	EN 60811-504 High low temperature resistance
	EN 60811-404 High oil resistance
	EN 60811-404 High fuel resistance
	EN 60811-404 Alkali resistance
	EN 60811-404 Acid resistance
	DIN 51900 Low fire load
	EN 50618 UV resistant

Commercial data

Packaging size	1
Net weight	600 g
Net weight	61 g/m
Country of origin	Switzerland
European customs tariff number	85444290
GTIN	5713140273351
eCl@ss	27061801 Data and communication cable (copper)
ETIM	EC003249



Pushing Performance
Since 1945

Commercial data

UNSPSC 24.0	26121609
-------------	----------