

PN Type B Hybrid 4xAWG22/7 + 4x1.5, 100m




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 600 0300
Specification	PN Type B Hybrid 4xAWG22/7 + 4x1.5, 100m
HARTING eCatalogue	https://harting.com/09456000300

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Hybrid cable (copper / copper)
Description of the cable	Flame retardant

Version

Cable length	100 m
Number of cores	8
Core structure	4x AWG 22/7 4x 1.5 mm ²

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-20 ... +70 °C
Coupling attenuation @ 20 °C / 10 MHz	≤10 mΩ/m
Conductor resistance @ 20 °C	≤120 Ω/km
Insulation resistance @ 20 °C	≥500 MΩ x km
Signal run time @ 20 °C	≤5.3 ns/m
Impedance @ 100 MHz	100 Ω ±15 %



Pushing Performance
Since 1945

Material properties

Material (cable)	FRNC (LSZH)
Colour (cable)	Green
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes

Specifications and approvals

Specifications	EN 13602 IEC 60332-1-2 Flame retardancy UL style 21282 (80 °C / 150 V)
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	15,000 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140061989
eCl@ss	27060501 Hybrid cable
ETIM	EC001579
UNSPSC 24.0	26121639