

HARTING IE Cat.6A 4x2xAWG26/7 PVC, 500m




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 600 0522
Specification	HARTING IE Cat.6A 4x2xAWG26/7 PVC, 500m
HARTING eCatalogue	https://harting.com/09456000522

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)
Description of the cable	Flame retardant UV resistant
Printing on cable	HARTING INDUSTRIAL CABLE CAT 6A PVC S/FTP 4x2xAWG26/7 E333435 "UR-Logo" AWM STYLE 20276 80°C 30V 09456000500020X "meter marking" "Charge Number" "HARTING LOGO"

Version

Cable length	500 m
Number of cores	8
Core structure	4x 2x AWG 26/7

Technical characteristics

Rated voltage	100 V
Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s
Loop resistance	≤290 Ω/km
Limiting temperature	-20 ... +80 °C



Pushing Performance
Since 1945

Technical characteristics

Cable diameter	6.3 ... 6.9 mm
Minimum bending radius	10x Cable diameter (repeated bending) 5x Cable diameter (singular bending)
Test voltage $U_{r.m.s.}$	0.7 kV Wire / wire / shielding
Conductor resistance @ 20 °C	$\leq 290 \Omega/\text{km}$
Insulation resistance @ 20 °C	$\geq 500 \text{ M}\Omega \times \text{km}$
Signal run time @ 20 °C	$\leq 5.13 \text{ ns/m}$
Impedance @ 100 MHz	$100 \Omega \pm 5 \%$

Material properties

Material (cable)	PVC
Colour (cable)	Yellow
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61156-6 EN 13602 IEC 60332-1-2 Flame retardancy UL style 20276 (80 °C / 30 V) UN/ECE-R 118 fire protection for rolling stock
----------------	--

Commercial data

Packaging size	1
Net weight	1 g
Net weight	47 g/m
Country of origin	Germany
European customs tariff number	85444995
GTIN	5713140062122
eCl@ss	27061801 Data and communication cable (copper)
ETIM	EC003249



Pushing Performance
Since 1945

Commercial data

UNSPSC 24.0	26121609
-------------	----------