

DSUB ANGLED EUR FEMALE STAMPED



Image is for illustration purposes only. Please refer to product description.

Identification

| | |
|----------------------------|-------------------|
| Category | Connectors |
| Series | D-Sub |
| Identification | Standard |
| Element | Connector |
| Description of the contact | Stamped Angled |

Version

| | |
|--------------------|------------------------------------|
| Termination method | Wave soldering termination |
| Gender | Female |
| Size | D-Sub 4 |
| Connection type | Motherboard to daughtercard |
| Number of contacts | 37 |
| Termination length | 2.9 mm |
| Locking type | Fixing flange with thread 4-40 UNC |

Technical characteristics

| | |
|------------------------------------|---------------------|
| Distance between rows | 2.54 mm |
| Contact spacing (termination side) | 2.76 mm |
| Rated current | 6.5 A |
| Clearance distance | ≥1 mm |
| Creepage distance | ≥1 mm |
| Insulation resistance | >10 ¹⁰ Ω |

Technical characteristics

| | |
|----------------------------------|---------------------------|
| Contact resistance | ≤10 mΩ |
| Tightening torque | ≤0.6 Nm Female screw lock |
| Limiting temperature | -55 ... +125 °C |
| Insertion force | ≤123 N |
| Withdrawal force | ≥11 N ≤82 N |
| Performance level | 3 |
| Mating cycles | ≥50 |
| Test voltage U _{r.m.s.} | 1 kV |
| Isolation group | IIIa (175 ≤ CTI < 400) |
| PCB thickness | ≥1.6 mm |
| Installation height | 7.3 mm |
| Hot plugging | No |

Material properties

| | |
|---|---|
| Material (insert) | Thermoplastic resin, glass-fibre filled (PBTP) Shell: Plated steel |
| Colour (insert) | Black |
| Material (contacts) | Copper alloy |
| Surface (contacts) | Noble metal over Ni |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Nickel |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R26 |

Specifications and approvals

| | |
|----------------|-----------|
| Specifications | DIN 41652 |
|----------------|-----------|

Specifications and approvals

| | |
|----------|-----------------------|
| UL / CSA | UL 1977 ECBT2.E102079 |
|----------|-----------------------|

Commercial data

| | |
|--------------------------------|------------------------|
| Packaging size | 50 |
| Net weight | 16.44 g |
| Country of origin | Romania |
| European customs tariff number | 85366990 |
| GTIN | 5713140084865 |
| eCl@ss | 27440214 D-Sub coupler |
| ETIM | EC001136 |
| UNSPSC 24.0 | 39121469 |