

D SUB SV FE IDC 15 AU3 with M3 nut



Image is for illustration purposes only. Please refer to product description.

Part number	09 66 218 7501
Specification	D SUB SV FE IDC 15 AU3 with M3 nut
HARTING eCatalogue	https://harting.com/09662187501

Identification

Category	Connectors
Series	D-Sub
Identification	Standard
Element	Connector
Description of the contact	Stamped Straight

Version

Termination method	IDC insulation displacement termination
Gender	Female
Size	D-Sub 2
Connection type	PCB to cable Cable to cable
Number of contacts	15
Locking type	Fixing flange with thread M3

Technical characteristics

Conductor cross-section	0.09 ... 0.13 mm ²
Conductor cross-section [AWG]	AWG 28 ... AWG 26
Rated current	2 A
Clearance distance	≥0.7 mm
Creepage distance	≥0.7 mm
Insulation resistance	>10 ¹⁰ Ω
Contact resistance	≤10 mΩ

Technical characteristics

Tightening torque ≤ 0.6 Nm Female screw lock

Limiting temperature $-55 \dots +125$ °C

Insertion force ≤ 50 N

Withdrawal force ≥ 4.5 N
 ≤ 33 N

Performance level 3

Mating cycles ≥ 50

Test voltage $U_{r.m.s.}$ 1 kV

Hot plugging No

Material properties

Material (insert) Thermoplastic resin, glass-fibre filled (PBTP)
Shell: Plated steel

Colour (insert) Black

Material (contacts) Copper alloy

Surface (contacts) Noble metal over Ni

Material flammability class acc. to UL 94 V-0

RoHS compliant with exemption

RoHS exemptions 6(c): Copper alloy containing up to 4 % lead by weight

ELV status compliant with exemption

China RoHS 50

REACH Annex XVII substances Not contained

REACH ANNEX XIV substances Not contained

REACH SVHC substances Yes

REACH SVHC substances Lead

ECHA SCIP number ecef7555-f643-4ceb-a337-fc54762297f1

California Proposition 65 substances Yes

California Proposition 65 substances Lead

Specifications and approvals

Specifications DIN 41652

UL / CSA UL 1977 ECBT2.E102079

Commercial data

Packaging size 100

Page 2 / 3 | Creation date 2025-07-24 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany

Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Commercial data

Net weight	10.99 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140082038
eCl@ss	27440214 D-Sub coupler
ETIM	EC001136
UNSPSC 24.0	39121469