

## Han-Yellock shell top entry M40



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 11 12 600 1403                                                                |
| Specification      | Han-Yellock shell top entry M40                                               |
| HARTING eCatalogue | <a href="https://harting.com/11126001403">https://harting.com/11126001403</a> |

### Identification

|                          |                  |
|--------------------------|------------------|
| Category                 | Hoods / Housings |
| Series of hoods/housings | Han-Yellock®     |
| Type of hood/housing     | Shell            |

### Version

|                         |                                            |
|-------------------------|--------------------------------------------|
| Size                    | Han-Yellock® 60                            |
| Version                 | Top entry                                  |
| Number of cable entries | 1                                          |
| Cable entry             | 1x M40                                     |
| Locking type            | Push button                                |
| Field of application    | Hoods/housings for industrial applications |

### Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Un-/locking temperature                | -10 ... +85 °C                                 |
| Degree of protection acc. to IEC 60529 | IP65<br>IP67                                   |

### Material properties

|                         |                       |
|-------------------------|-----------------------|
| Material (hood/housing) | Aluminium die-cast    |
| Surface (hood/housing)  | Powder-coated         |
| Colour (hood/housing)   | RAL 7021 (black grey) |



**Pushing Performance**  
Since 1945

## Material properties

|                                           |                       |
|-------------------------------------------|-----------------------|
| Material flammability class acc. to UL 94 | V-0                   |
| RoHS                                      | compliant             |
| ELV status                                | compliant             |
| China RoHS                                | e                     |
| REACH Annex XVII substances               | Not contained         |
| REACH ANNEX XIV substances                | Not contained         |
| REACH SVHC substances                     | Not contained         |
| California Proposition 65 substances      | Yes                   |
| California Proposition 65 substances      | Nickel<br>Naphthalene |

## Specifications and approvals

|                |                          |
|----------------|--------------------------|
| Specifications | IEC 60664-1<br>IEC 61984 |
| Approvals      | CE<br>DNV GL             |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 143.8 g                                  |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140110359                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |