

Han-Yellock 10 bulkhead mount housing



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 11 20 003 0300 |
| Specification | Han-Yellock 10 bulkhead mount housing |
| HARTING eCatalogue | https://harting.com/11200030300 |

Identification

| | |
|-----------------------------|--------------------------|
| Category | Hoods / Housings |
| Series of hoods/housings | Han-Yellock® |
| Type of hood/housing | Bulkhead mounted housing |
| Description of hood/housing | Straight |

Version

| | |
|----------------------|--|
| Size | Han-Yellock® 10 |
| Locking type | Push button |
| Field of application | Hoods/housings for industrial applications |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -40 ... +125 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Un-/locking temperature | -10 ... +85 °C |
| Degree of protection acc. to IEC 60529 | IP65 IP67 |

Material properties

| | |
|---|---------------|
| Material (hood/housing) | Zinc die-cast |
| Surface (hood/housing) | Passivated |
| Colour (hood/housing) | Metallic |
| Material (seal) | NBR |
| Material flammability class acc. to UL 94 | V-0 |

Material properties

| | |
|--------------------------------------|----------------|
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead Nickel |

Specifications and approvals

| | |
|----------------|--------------------------|
| Specifications | IEC 60664-1 IEC 61984 |
| Approvals | CE DNV GL |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 40 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140110625 |
| eCl@ss | 27440202 Shell for industrial connectors |
| ETIM | EC000437 |
| UNSPSC 24.0 | 39121466 |