

Han 6HPR-HSMA2-for SCL-M25




Image is for illustration purposes only. Please refer to product description.

Part number	19 40 006 0915
Specification	Han 6HPR-HSMA2-for SCL-M25
HARTING eCatalogue	https://harting.com/19400060915

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® HPR
Type of hood/housing	Surface mounted housing
Description of hood/housing	Horizontal version

Version

Size	6 B
Version	Top entry
Number of cable entries	2
Cable entry	2x M25
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Stainless steel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	900 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140172845
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466