

## Han 24HPR-enlarged-HTE3-SCL-M32/M25



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han® HPR enlarged
Type of hood/housing	Hood

### Version

Size	24 HPR enlarged
Version	Top entry
Number of cable entries	3
Cable entry	1x M25 2x M32
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments
Details	When using Han® Standard inserts of size B or Han-Modular® hinged frames, please order adapter 09400009960 separately.

### Technical characteristics

Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
	IP65
Degree of protection acc. to IEC 60529	IP68
	IP69 / IPX9K acc. to ISO 20653

## Technical characteristics

Type rating acc. to UL 50 / UL 50E	4 4X 12
------------------------------------	---------------

## Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	767.5 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140173279
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466