

## Han-INOX® 6B-HTE-M25 f.SL



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 19 44 006 0446                                                                |
| Specification      | Han-INOX® 6B-HTE-M25 f.SL                                                     |
| HARTING eCatalogue | <a href="https://harting.com/19440060446">https://harting.com/19440060446</a> |

### Identification

|                          |                  |
|--------------------------|------------------|
| Category                 | Hoods / Housings |
| Series of hoods/housings | Han-INOX®        |
| Type of hood/housing     | Hood             |

### Version

|                         |                                       |
|-------------------------|---------------------------------------|
| Size                    | 6 B                                   |
| Version                 | Top entry                             |
| Number of cable entries | 1                                     |
| Cable entry             | 1x M25                                |
| Locking type            | Single locking lever                  |
| Field of application    | Hoods/housings for harsh environments |

### Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65                                           |
| Type rating acc. to UL 50 / UL 50E     | 4                                              |
|                                        | 4X                                             |
|                                        | 12                                             |

### Material properties

|                         |                 |
|-------------------------|-----------------|
| Material (hood/housing) | Stainless steel |
| Surface (hood/housing)  | Uncoated        |
| Colour (hood/housing)   | Unpainted       |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |               |
|--------------------------------------|---------------|
| RoHS                                 | compliant     |
| ELV status                           | compliant     |
| China RoHS                           | e             |
| REACH Annex XVII substances          | Not contained |
| REACH ANNEX XIV substances           | Not contained |
| REACH SVHC substances                | Not contained |
| California Proposition 65 substances | Not contained |

## Specifications and approvals

|           |                                   |
|-----------|-----------------------------------|
| UL / CSA  | UL 1977 ECBT2.E235076             |
|           | CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE<br>DNV GL                      |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 1 g                                      |
| Country of origin              | Romania                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140829602                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |