

DSUB FE RIGHT ANG HIGH VOLTAGE CONTACT




Image is for illustration purposes only. Please refer to product description.

Part number	09 69 581 2550
Specification	DSUB FE RIGHT ANG HIGH VOLTAGE CONTACT
HARTING eCatalogue	https://harting.com/09695812550

Identification

Category	Contacts
Series	D-Sub
Identification	Mixed
Type of contact	Solder contact
Description of the contact	Angled

Version

Termination method	Solder termination
Termination method	Solder termination
Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.25 ... 0.5 mm ²
Conductor cross-section [AWG]	AWG 24 ... AWG 20
Rated current	≤10 A
Rated voltage	≤3,000 V >1,000 V
Contact resistance	≤3 mΩ
Stripping length	2.5 mm
Limiting temperature	-55 ... +125 °C
Insertion force	≤5 N
Withdrawal force	≈2.5 N



Pushing Performance
Since 1945

Technical characteristics

Performance level	AU 50 1
Mating cycles	≥500
Test voltage $U_{r.m.s.}$	4 kV @ 50 Hz

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni
Layer thickness	≥1.27 µm
Layer thickness	≥50 µinch
Material (hood/housing)	Polycarbonate / Teflon (PTFE)
Material (locking)	PI
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	20
Net weight	1.57 g
Country of origin	Czechia
European customs tariff number	85366990
GTIN	5713140102651
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796



Pushing Performance
Since 1945

Commercial data

UNSPSC 24.0	39121522
-------------	----------
