

## Han HPR HPTC 1400 CS UNSH IP65/67 185



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Connector sets
Series of hoods/housings	Han® HPR HPTC
Type of hood/housing	Complete set
Description of hood/housing	Cable side With integrated cable gland
Type of cable	Copper cable (round)

### Version

Size	3
Shielding	360° shielding
Coding	16 coding options
Number of cable entries	2
Cable entry	2x M40
Field of application	Hoods/housings for harsh outdoor environments

### Technical characteristics

Conductor cross-section	185 mm <sup>2</sup>
Rated current	1,400 A
Rated voltage	3,600 V
Rated impulse voltage	20 kV
Pollution degree	4
Overvoltage category	III
Limiting temperature	-40 ... +125 °C

## Technical characteristics

Mating cycles	≥25
Degree of protection acc. to IEC 60529	IP68
	IP66
	IP69
Clamping range	20.5 ... 25 mm

## Material properties

Material (insert)	Polyamide (PA)
Material (hood/housing)	Aluminium die-cast Corrosion resistant
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	4141b1b0-d696-48fb-8ad9-5046cd2452df
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	EN 50467 EN 50124-1 IEC 61373 Category 1 Class B EN 45545 EN 60137
----------------	--

## Commercial data

Packaging size	1
Net weight	2,300 g
Country of origin	Germany
European customs tariff number	85359000
GTIN	5713140190023
eCl@ss	27440113 Rectangular connectors (set)

## Commercial data

ETIM	EC002636
UNSPSC 24.0	39121408