

## M12-CON-1.0-AWG26-23/0,13-0,25mm<sup>2</sup>-F



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9984
Specification	M12-CON-1.0-AWG26-23/0,13-0,25mm <sup>2</sup> -F
HARTING eCatalogue	<a href="https://harting.com/21011009984">https://harting.com/21011009984</a>

### Identification

Category	Contacts
Series	Circular connectors M12
Identification	Power
Type of contact	Crimp contact

### Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.13 ... 0.25 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 26 ... AWG 23
Performance level	1

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Commercial data

Packaging size	100
Net weight	0.1 g
Country of origin	Switzerland
European customs tariff number	85366990
GTIN	5713140229525
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522