

## har-flex distance adapter 22mm 50P PL1



Image is for illustration purposes only. Please refer to product description.

Part number	15 16 050 2010 041
Specification	har-flex distance adapter 22mm 50P PL1
HARTING eCatalogue	<a href="https://harting.com/15160502010041">https://harting.com/15160502010041</a>

### Identification

Category	Connectors
Series	har-flex®
Identification	Signal
Element	Adapter
Description of the contact	Male contact Male contact

### Version

Connection type	Mezzanine Cable to cable
Number of contacts	50
Termination length	2.5 mm
Pack contents	28 pieces in a tray 5 trays per box

### Technical characteristics

Contact rows	2
Contact spacing (mating side)	1.27 mm
Stacking height	22 mm
Clearance distance	≥0.4 mm
Creepage distance	≥0.4 mm
Insulation resistance	>10 <sup>9</sup> Ω
Contact resistance	<35 mΩ
Limiting temperature	-55 ... +125 °C

## Technical characteristics

Insertion force	≤25 N
Withdrawal force	≤25 N
Performance level	1
Mating cycles	≥500
Test voltage $U_{r.m.s.}$	0.5 kV
Isolation group	IIIa ( $175 \leq CTI < 400$ )
Wiping length	1.5 mm

## Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

UL / CSA	UL in preparation
----------	-------------------

## Commercial data

Packaging size	140
Net weight	3.84 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140306899
eCl@ss	27460201 PCB connector (board connector)
UNSPSC 24.0	39121415