

har-flex Hybrid F ang 8+36 SMT PL1 400pc



Image is for illustration purposes only. Please refer to product description.

Part number	15 85 836 2601 000
Specification	har-flex Hybrid F ang 8+36 SMT PL1 400pc
HARTING eCatalogue	https://harting.com/15858362601000

Identification

Category	Connectors
Series	har-flex®
Identification	Hybrid
Element	Female connector
Description of the contact	Angled

Version

Termination method	Reflow soldering termination (SMT)
Connection type	Motherboard to daughtercard Extender card
Number of contacts	44
Number of signal contacts	36
Number of power contacts	8
Pack contents	400 pieces on reel

Technical characteristics

Contact spacing (termination side)	1.27 mm 2.54 mm
Contact spacing (mating side)	1.27 mm 2.54 mm
Rated current	22.5 A
Rated voltage	50 V AC 120 V DC
Rated voltage	acc. to IEC 60664-1

Technical characteristics

Rated impulse voltage	1.5 kV
Pollution degree	2
Clearance distance	≥ 0.4 mm Signal contacts ≥ 1.74 mm Power contacts ≥ 1.11 mm Signal to power contacts
Creepage distance	≥ 0.4 mm PCB: Signal contacts ≥ 1.74 mm PCB: Power contacts ≥ 1.11 mm PCB: Signal to power contacts ≥ 0.4 mm Connector: Signal contacts ≥ 1.89 mm Connector: Power contacts ≥ 2.09 mm Connector: Signal to power contacts
Insulation resistance	$>10^{10}$ Ω
Contact resistance	≤ 25 m Ω
Limiting temperature	-55 ... +125 °C
Performance level	1
Mating cycles	≥ 500
Test voltage $U_{r.m.s.}$	0.5 kV Signal 1.39 kV Signal / Power 1.39 kV Power / Power
Isolation group	IIIa ($175 \leq CTI < 400$)
Moisture Sensitivity Level (MSL)	1 acc. to ECA/IPC/JEDEC J-STD-020D
Process Sensitivity Level (PSL)	R0 acc. to ECA/IPC/JEDEC J-STD-020D
Coplanarity of contacts	0.12 mm

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Sn over Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Material properties

California Proposition 65 substances	Not contained
--------------------------------------	---------------

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
----------	--

Commercial data

Packaging size	1
Net weight	2,638 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140205239
eCl@ss	27460201 PCB connector (board connector)
ETIM	EC002637
UNSPSC 24.0	39121415