

Adapter M12 RJ45 Cat 6a angled



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Series	Circular connectors M12 RJ45
Connector 1	Female 8 poles RJ45
Type of accessory	Adapter
Description of the accessory	Panel feed through

Version

Gender	Female
Coding	X-coding

Technical characteristics

Rated current	0.5 A
Rated voltage	48 V AC 60 V DC
Transmission characteristics	Cat. 6A Class EA up to 500 MHz
Data rate	10 Mbit/s 10 Gbit/s
Limiting temperature	-40 ... +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Thickness of the panel	2.1 ... 4.5 mm

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Zinc die-cast
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 61076-2-109
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	48 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140138391
eCl@ss	27440190 Industry connector (unspecified)
ETIM	EC001264

Commercial data

UNSPSC 24.0

39121409