

## M12 SD PFT Male X cod 8 pol



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 881 1825
Specification	M12 SD PFT Male X cod 8 pol
HARTING eCatalogue	<a href="https://harting.com/21038811825">https://harting.com/21038811825</a>

### Identification

Category	Connectors
Series	Circular connectors M12
Identification	Slim Design
Element	Cable connector Panel feed through
Specification	for rear mounting

### Version

Termination method	Crimp termination
Gender	Male
Shielding	Shielded
Number of contacts	8
Coding	X-coding
Locking type	Screw locking PushPull
Details	Please order crimp contacts separately.
Details	For Ethernet applications up to 10 Gbit only

### Technical characteristics

Conductor cross-section	0.08 ... 0.25 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 28 ... AWG 23
Wire outer diameter	≤1.4 mm
Rated current	0.5 A
Rated voltage	48 V

## Technical characteristics

Rated impulse voltage	0.8 kV
Pollution degree	3
Transmission characteristics	Cat. 6A Class EA up to 500 MHz
Overvoltage category	III
	10 Mbit/s
	100 Mbit/s
Data rate	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Insulation resistance	>10 <sup>8</sup> Ω
Contact resistance	≤10 mΩ
Tightening torque	2 Nm Lock nut
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	5.7 ... 8.8 mm
Isolation group	I (600 ≤ CTI)

## Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	no requirements (flammable mass < 10g)

## Specifications and approvals

Specifications	IEC 61076-2-109 IEC 61076-2-010
----------------	------------------------------------

## Commercial data

Packaging size	1
Net weight	38.7 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140226067
eCl@ss	27440116 Circular connector (for field assembly)
ETIM	EC002635
UNSPSC 24.0	39121413