

## har-bus HM FL. Typ AB19 ohne Schirmblech




Image is for illustration purposes only. Please refer to product description.

Part number	17 33 095 2101
Specification	har-bus HM FL. Typ AB19 ohne Schirmblech
HARTING eCatalogue	<a href="https://harting.com/17330952101">https://harting.com/17330952101</a>

### Identification

Category	Connectors
Series	har-bus <sup>®</sup> HM
Identification	Type AB19
Element	Female connector
Description of the contact	Angled

### Version

Termination method	Press-in termination
Connection type	Motherboard to daughtercard
Number of contacts	95
Pack contents	Tube

### Technical characteristics

Contact rows	7
Contact spacing (termination side)	2 mm
Contact spacing (mating side)	2 mm
Rated current	1 A
Data rate	≤2,500 Mbit/s
Insulation resistance	>10 <sup>9</sup> Ω
Contact resistance	≤20 mΩ
Limiting temperature	-55 ... +125 °C
Insertion force	≤71.25 N
Withdrawal force	≥14.25 N



Pushing Performance  
Since 1945

## Technical characteristics

Performance level	2
Test voltage $U_{r.m.s.}$	0.75 kV
Isolation group	IIIa ( $175 \leq CTI < 400$ )
PCB thickness	$\geq 1.4$ mm

## Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled
Colour (insert)	Beige
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
----------	--

## Commercial data

Packaging size	13
Net weight	15 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140122154
eCl@ss	27460201 PCB connector (board connector)
ETIM	EC002637



**Pushing Performance**  
Since 1945

## Commercial data

UNSPSC 24.0

39121415

---