

M12-SD-CC-CRIMP-8P-XCOD-F-STR-CF



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 881 2841
Specification	M12-SD-CC-CRIMP-8P-XCOD-F-STR-CF
HARTING eCatalogue	https://harting.com/21038812841

Identification

Category	Connectors
Series	Circular connectors M12
Identification	Slim Design PushPull
Element	Cable connector Panel feed through
Specification	Straight

Version

Termination method	Crimp termination
Gender	Female
Shielding	Shielded Shield connection with crimp flange
Number of contacts	8
Coding	X-coding
Locking type	Screw locking PushPull
Details	Please order crimp contacts separately.
Details	For Ethernet applications up to 10 Gbit only

Technical characteristics

Conductor cross-section	0.08 ... 0.25 mm ²
Conductor cross-section [AWG]	AWG 28 ... AWG 23
Wire outer diameter	≤1.4 mm



Pushing Performance
 Since 1945

Technical characteristics

Rated current	0.5 A
Rated voltage	48 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz
Overvoltage category	III
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
Insulation resistance	10 Gbit/s
	>10 ⁸ Ω
Contact resistance	≤10 mΩ
Tightening torque	0.6 Nm
Wrench size (knurled screw / knurled nut)	15
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Isolation group	I (600 ≤ CTI)

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (hood/housing)	Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel



Pushing Performance
Since 1945

Material properties

Fire protection on railway vehicles EN 45545-2 (2020-08) + A1 (2023-10)

Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)
------------------------------------	------------------------------

Specifications and approvals

Specifications	IEC 61076-2-109
----------------	-----------------

Commercial data

Packaging size	1
----------------	---

Net weight	52.1 g
------------	--------

Country of origin	Romania
-------------------	---------

European customs tariff number	85366990
--------------------------------	----------

GTIN	5713140226142
------	---------------

eCl@ss	27440116 Circular connector (for field assembly)
--------	--

ETIM	EC002635
------	----------

UNSPSC 24.0	39121413
-------------	----------