

M12-P-CC-CRIMP S COD-M-STR-SHLD



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 896 1415
Specification	M12-P-CC-CRIMP S COD-M-STR-SHLD
HARTING eCatalogue	https://harting.com/21038961415

Identification

Category	Connectors
Series	Circular connectors M12
Identification	Power
Element	Cable connector
Specification	Straight

Version

Termination method	Crimp termination
Gender	Male
Shielding	Shielded
Number of contacts	4
Number of power contacts	3
Number of special contacts	1x PE contact
Coding	S-coding
Locking type	Screw locking
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.5 ... 2.5 mm ²
Rated current	12 A
Rated voltage	630 V
Rated impulse voltage	6 kV
Pollution degree	3

Technical characteristics

Overvoltage category	III
Insulation resistance	>10 ⁸ Ω
Contact resistance	≤10 mΩ
Tightening torque	0.6 Nm
Wrench size (knurled screw / knurled nut)	17
Limiting temperature	-40 ... +125 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	5.1 ... 10.1 mm
Isolation group	I (600 ≤ CTI)

Material properties

Material (insert)	Polyamide (PA)
Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 61076-2-111
----------------	-----------------

Commercial data

Packaging size	1
Net weight	6 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140227347
eCl@ss	27440116 Circular connector (for field assembly)

Commercial data

ETIM	EC002635
UNSPSC 24.0	39121413