



Pushing Performance
Since 1945

M12 X-coded Cable Assembly 3m



Image is for illustration purposes only. Please refer to product description.

Part number	21 33 010 0850 030
Specification	M12 X-coded Cable Assembly 3m
HARTING eCatalogue	https://harting.com/21330100850030

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 X-coding Male Straight
Type of cable	Copper cable (round)

Version

Cable length	3 m
Number of cores	8
Core structure	4x 2 Twisted Pair
Shielding	Shielded
Coding	X-coding

Technical characteristics

Transmission characteristics	Cat. 6A Class E _A up to 500 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-40 ... +70 °C



Pushing Performance
Since 1945

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Yellow
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	2
Net weight	191 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140140202
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600