

M12 A-cod 5-pol st/- m/- PVC Dnet 1.0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 35 51A 0564 010
Specification	M12 A-cod 5-pol st/- m/- PVC Dnet 1.0m
HARTING eCatalogue	https://harting.com/213551A0564010

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 A-coding Male Straight
Type of cable	Copper cable (round)
Features	Colour coding: blue/white (AWG 24) and black/red (AWG 22)

Version

Cable length	1 m
Number of cores	5
Core structure	1x 2x AWG 22/19 1x 2x AWG 24/19
Shielding	Fully shielded, 360° shielding contact
Coding	A-coding

Technical characteristics

Transmission characteristics	DeviceNet
Cable diameter	6.9 mm $\pm$ 0.3 mm
Impedance	120 Ω



Pushing Performance
Since 1945

Technical characteristics

Conductor resistance @ 20 °C	≤85 Ω/km AWG 24
	≤54 Ω/km AWG 22
	≤9.75 Ω/km Shielding

Material properties

Material (shielding)	Aluminium
Material (cable)	PVC
Colour (cable)	Grey

Commercial data

Packaging size	1
Net weight	70 g
Country of origin	Mexico
GTIN	5713140238619
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC001855
UNSPSC 24.0	26121604