

## Han 16HPR EasyCon cover 3XM32



Image is for illustration purposes only. Please refer to product description.

Part number	19 40 016 9903
Specification	Han 16HPR EasyCon cover 3XM32
HARTING eCatalogue	<a href="https://harting.com/19400169903">https://harting.com/19400169903</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han® HPR EasyCon
Type of hood/housing	Mounting cover
Description of hood/housing	for surface mounted housings for hoods

### Version

Size	16 B
Number of cable entries	3
Cable entry	3x M32
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments
Details	Not compatible to cable glands 19 00 000 5014, 19 00 000 5015 and 19 00 000 5022

### Technical characteristics

Tightening torque	6 Nm Mounting cover 6 Nm Distance bolt 6 Nm Fixing screws
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653

## Technical characteristics

Type rating acc. to UL 50 / UL 50E	4 4X 12
------------------------------------	---------------

## Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	191.75 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140175259
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466