

Han-Eco Mod.16-C-f. HTE/HSE



Image is for illustration purposes only. Please refer to product description.

Part number	19 41 016 5406
Specification	Han-Eco Mod.16-C-f. HTE/HSE
HARTING eCatalogue	https://harting.com/19410165406

Identification

Category	Accessories
Series of hoods/housings	Han-Eco® Modular
Type of accessory	Protection cover
Description of the accessory	for hoods

Version

Size	16 B
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	RAL 9005 (jet black)
Material (locking)	Polyamide (PA) Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0



Pushing Performance
Since 1945

Material properties

Material flammability class acc. to UL 94
(locking levers)

V-0

RoHS

compliant

ELV status

compliant

China RoHS

e

REACH Annex XVII substances

Not contained

REACH ANNEX XIV substances

Not contained

REACH SVHC substances

Not contained

Fire protection on railway vehicles

EN 45545-2 (2020-08) + A1 (2023-10)

Requirement set with Hazard Levels

R22 (HL 1-3)
R23 (HL 1-3)

Specifications and approvals

Specifications

IEC 61984
EN 45545-2 Fire protection on railway vehicles

UL / CSA

UL 1977 ECBT2.E235076
CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size

1

Net weight

70 g

Country of origin

Germany

European customs tariff number

85389099

GTIN

5713140131088

eCl@ss

27440208 Cap for industrial connectors

ETIM

EC002314

UNSPSC 24.0

39121467