

M12 X-cod 8-pol st/st m/m PVC PP 5.0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 40 606 0885 050
Specification	M12 X-cod 8-pol st/st m/m PVC PP 5.0m
HARTING eCatalogue	https://harting.com/21406060885050

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 X-coding Male Straight
Connector 2	M12 X-coding Male Straight
Type of cable	Copper cable (round)

Version

Cable length	5 m
Number of cores	8
Core structure	4x 2x AWG 26/7
Shielding	Shielded
Number of contacts	8
Coding	X-coding
Locking type	PushPull

Technical characteristics

Rated current	0.5 A
Rated voltage	48 V AC 60 V DC
Transmission characteristics	Cat. 6A Class E _A up to 500 MHz



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-20 ... +80 °C moved -20 ... +80 °C unmoved
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	6.6 mm ± 0.3 mm
Minimum bending radius	4x Cable diameter (singular bending) 8x Cable diameter (repeated bending)

Material properties

Material (cable)	PVC
Colour (cable)	Yellow
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Triphenyl phosphate
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	UN/ECE-R 118
----------------	--------------

Commercial data

Packaging size	1
Net weight	95 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140490642
eCl@ss	27060390 Ready-made data cable (unspecified)
UNSPSC 24.0	26121600