

Ha-VIS eCon 2030BT-A



Image is for illustration purposes only. Please refer to product description.

Part number	24 02 003 0000
Specification	Ha-VIS eCon 2030BT-A
HARTING eCatalogue	https://harting.com/24020030000

Identification

Series	Ha-VIS eCon 2000
Element	Industrial Ethernet Switches
Specification	Unmanaged
Type of Ethernet	Fast Ethernet

Version

Total number of ports	3
Fixing	35 mm DIN rail acc. to EN 60715
Switching technology	Store and Forward
Frame size	1.522 kB
MAC table size	1k Entries
Packet buffer size	0.44 Megabit
Non blocking	Yes
Quality of service	Yes
Energie Efficient Ethernet	Yes
Flow control	Off
Signal contact	No
PoE functionality	No
Pack contents	Pluggable screw contact for power supply Assembly instructions

Termination data

Nominal voltage	24 V DC 48 V DC
-----------------	--------------------



Pushing Performance
Since 1945

Termination data

Permissible voltage	9 ... 60 V DC
Surge protection	Yes
Operating current	<32 mA @ 24 V DC <17 mA @ 48 V DC
Supply circuit	SELV (Circuit Breaker 10 A)
Starting current	<2.8 A @ 24 V DC <5.6 A @ 48 V DC
Overcurrent protection	2 A at input
Power consumption	<0.77 W @ 24 V DC
Termination method	Pluggable screw contact
Number of contacts	3
Conductor cross-section	0.08 ... 2.5 mm ²
Conductor cross-section [AWG]	AWG 28 ... AWG 12
Pinout	+ / - / FE
Reverse polarity protection	Yes

Technical characteristics

Operating temperature	-40 ... +70 °C
Storage temperature	-40 ... +85 °C
Relative humidity	0 ... 95 % Non-condensing (operation) 0 ... 95 % Non-condensing (storage/transport)
Air pressure	≥795 hPa ≈ 2000 m
Degree of protection acc. to IEC 60529	IP30 mated condition
MTBF	≈3,130,000 h

Ethernet ports copper

10/100 Mbit/s (RJ45-Ports)	3
Transmission standard	10BASE-Te 100BASE-TX EEE
Auto-negotiation	Yes
Auto-polarity	Yes
Auto-MDI(X)	Yes
Transmission physics	Twisted Pair Cat. 5
Data rate	10 Mbit/s 100 Mbit/s



Pushing Performance
 Since 1945

Ethernet ports copper

Transmission length 100 m

Material properties

Material (hood/housing)	Aluminium (anodised)
Length	27.3 mm
Width	46.5 mm
Height	113.5 mm
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	EN 55022 Radio disturbance characteristics
	EN 61000-4-2 Electrostatic discharge (ESD)
	EN 61000-4-3 Electromagnetic field
	EN 61000-4-4 Rapid transients (burst)
	EN 61000-4-5 Surge voltages
	EN 61000-4-6 conducted disturbances
	EN 61000-6-4 emission standard
	IEC 60068-2-6 Vibration (sinusoidal)
	IEEE 802.3
UL / CSA	UL 508 NRAQ.E253944
	CSA-C22.2 No. 142 NRAQ7.E253944
Approvals	CE
	DNV GL
FCC	Yes

Commercial data

Packaging size	1
----------------	---



Pushing Performance
Since 1945

Commercial data

Net weight	197 g
Country of origin	Germany
European customs tariff number	85176200
GTIN	5713140147133
eCl@ss	19170130 Network switch (general application)
ETIM	EC000734
UNSPSC 24.0	43222612