

## Ha-VIS eCon 3026 GBT-AT1-SPE



Image is for illustration purposes only. Please refer to product description.

### Identification

Series	Ha-VIS eCon 3000
Identification	Single Pair Ethernet (SPE)
Element	Industrial Ethernet Switches
Specification	Unmanaged
Type of Ethernet	Gigabit Ethernet

### Version

Total number of ports	8
Fixing	35 mm DIN rail acc. to EN 60715
Switching technology	Store and Forward
Frame size	10.24 kB
MAC table size	1k Entries
MAC-address filter	LLDP and PROFINET PTCP Delay (01-80-C0-00-00-0E) blocked
Packet buffer size	1 Megabit
Non blocking	Yes
Quality of service	Yes
Signal contact	No
PoE functionality	No
Jumbo frame support	Yes
Field of application	Indoor usage
Pack contents	Pluggable screw contact for power supply Assembly instructions

## Termination data

Nominal voltage	24 V DC 48 V DC
Permissible voltage	16.8 ... 60 V DC
Surge protection	Yes
Operating current	145 mA @ 24 V DC 76 mA @ 48 V DC
Supply circuit	SELV (Circuit Breaker 10 A)
Starting current	<1.3 A @ 24 V DC <2.2 A @ 48 V DC
Overcurrent protection	2 A at input
Power consumption	<3.5 W @ 24 V DC
Termination method	Pluggable screw contact
Number of contacts	3
Conductor cross-section	0.08 ... 2.5 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 28 ... AWG 12
Pinout	+ / - / FE
Reverse polarity protection	Yes

## Technical characteristics

Pollution degree	2
Overvoltage category	II (400 ≤ CTI < 600)
Operating temperature	-40 ... +70 °C
Storage temperature	-40 ... +85 °C
Relative humidity	0 ... 95 % Non-condensing (operation) 0 ... 95 % Non-condensing (storage/transport)
Air pressure	≥795 hPa ≈ 2000 m
Degree of protection acc. to IEC 60529	IP30 mated condition

## Ethernet ports copper

10/100/1000 Mbit/s (RJ45-Ports)	2
1000 Mbit/s (RJ45-Ports)	2
Transmission standard	10BASE-T 100BASE-TX 1000BASE-T
Auto-negotiation	Yes
Auto-polarity	Yes

### Ethernet ports copper

Auto-MDI(X)	Yes
Transmission physics	Twisted Pair Cat. 5
Data rate	10 Mbit/s 100 Mbit/s 1,000 Mbit/s
Transmission length	100 m

### Ethernet ports SPE

100 Mbit/s (SPE-Ports)	5
1000 Mbit/s (SPE-Ports)	1
Transmission standard	100BASE-T1 1000BASE-T1
Transmission physics	Twisted Pair 2 wires Twisted Pair 2 wires
Data rate	100 Mbit/s 1,000 Mbit/s
Transmission length	40 m 40 m
Configuration Master-Slave	via DIP-Switch via DIP-Switch

### Material properties

Material (hood/housing)	Aluminium (anodised) Stainless steel
Length	64.5 mm
Width	33 mm
Height	130 mm
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	EN 55032 emission standard EN 55035 EMC Interference immunity EN 61000-4-2 Electrostatic discharge (ESD) EN 61000-4-3 Electromagnetic field EN 61000-4-4 Rapid transients (burst) EN 61000-4-5 Surge voltages EN 61000-4-6 conducted disturbances EN 61000-6-4 emission standard IEC 60068-2-6 Vibration (sinusoidal)
Approvals	CE on request
PROFINET	Yes
FCC	Yes

## Commercial data

Packaging size	1
Net weight	348 g
Country of origin	Germany
European customs tariff number	85176200
GTIN	5713140195226
eCl@ss	19170130 Network switch (general application)
ETIM	EC000734
UNSPSC 24.0	43222612