

## Acces. Special Cable Clamp EMC M32



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 19 62 000 5096                                                                |
| Specification      | Acces. Special Cable Clamp EMC M32                                            |
| HARTING eCatalogue | <a href="https://harting.com/19620005096">https://harting.com/19620005096</a> |

### Identification

|                              |             |
|------------------------------|-------------|
| Category                     | Accessories |
| Type of accessory            | Cable gland |
| Description of the accessory | EMC version |

### Technical characteristics

|                                        |                 |
|----------------------------------------|-----------------|
| Wrench size                            | 35              |
| Limiting temperature                   | -40 ... +130 °C |
| Degree of protection acc. to IEC 60529 | IP68            |
| Size                                   | M32             |
| Clamping range                         | 14 ... 18 mm    |
| Shielding diameter                     | 9 ... 14.5 mm   |
| Width across corners                   | 38.5 mm         |

### Material properties

|                             |                                                        |
|-----------------------------|--------------------------------------------------------|
| Material (cable glands)     | Metal                                                  |
| RoHS                        | compliant with exemption                               |
| RoHS exemptions             | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                  | compliant with exemption                               |
| China RoHS                  | 50                                                     |
| REACH Annex XVII substances | Not contained                                          |
| REACH ANNEX XIV substances  | Not contained                                          |
| REACH SVHC substances       | Yes                                                    |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                                                             |
|--------------------------------------|-----------------------------------------------------------------------------|
| REACH SVHC substances                | Lead                                                                        |
|                                      | 2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326) |
| California Proposition 65 substances | Yes                                                                         |
| California Proposition 65 substances | Lead                                                                        |
|                                      | Nickel                                                                      |

## Commercial data

|                                |                                                    |
|--------------------------------|----------------------------------------------------|
| Packaging size                 | 10                                                 |
| Net weight                     | 96.66 g                                            |
| Country of origin              | Germany                                            |
| European customs tariff number | 74122000                                           |
| GTIN                           | 5713140132245                                      |
| eCl@ss                         | 27140803 Cable gland EMC (electrical installation) |
| ETIM                           | EC000441                                           |
| UNSPSC 24.0                    | 39121431                                           |