

## M12 Power male crimp contact PE 0,75mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9963
Specification	M12 Power male crimp contact PE 0,75mm <sup>2</sup>
HARTING eCatalogue	<a href="https://harting.com/21011009963">https://harting.com/21011009963</a>

### Identification

Category	Contacts
Series	Circular connectors M12
Identification	Power
Type of contact	Crimp contact

### Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.75 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 19
Performance level	1

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

## Commercial data

Packaging size	50
Net weight	0.298 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140229419
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522