

InduCom cable clamp 9-37pol hood 11-14mm



Image is for illustration purposes only. Please refer to product description.

Part number	61 03 000 0148
Specification	InduCom cable clamp 9-37pol hood 11-14mm
HARTING eCatalogue	https://harting.com/61030000148

Identification

Category	Accessories
Type of accessory	Cable clamp
Description of the accessory	D-Sub 1 ... 4

Technical characteristics

Ambient temperature	-20 ... +90 °C
Cable diameter	11 ... 14 mm

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Commercial data

Packaging size	1
----------------	---



Pushing Performance
Since 1945

Commercial data

Net weight	16 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140229693
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400