



Pushing Performance
Since 1945

Han-Mod_M_Carrier_C.1_Short




Image is for illustration purposes only. Please refer to product description.

Part number	97 00 000 0429
Specification	Han-Mod_M_Carrier_C.1_Short
HARTING eCatalogue	https://harting.com/97000000429

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Carrier Cube
Size of the module	Domino module
Description of the module	Short version Small tab

Version

Details	Insulated to the hinged frame.
---------	--------------------------------

Technical characteristics

Limiting temperature	-40 ... +85 °C
----------------------	----------------

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	2
Country of origin	Romania
European customs tariff number	85389099
eCl@ss	27440217 Module for industrial connectors (power/signals)