

M12 A-cod 5-pol st /st m /f PVC 2.00m



Image is for illustration purposes only. Please refer to product description.

Part number	C2 13 200 0000 0021
Specification	M12 A-cod 5-pol st /st m /f PVC 2.00m
HARTING eCatalogue	https://harting.com/C21320000000021

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 A-coding Male Straight Overmoulded
Connector 2	M12 A-coding Female Straight Overmoulded
Type of cable	Copper cable (round)

Version

Cable length	2 m
Number of cores	5
Core structure	5x 0.34 mm ²
Termination method	Crimp termination
Shielding	Unshielded
Coding	A-coding

Technical characteristics

Rated current	4 A
Rated voltage	60 V
Limiting temperature	-25 ... +80 °C moved -40 ... +80 °C unmoved



Pushing Performance
Since 1945

Technical characteristics

Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	5.3 mm

Material properties

Material (cable)	PVC
Colour (cable)	RAL 7040 (Window grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61076-2-101
	UL 1581
	IEC 60332-2-2 Flame retardancy
UL / CSA	UL in preparation
Approvals	CE

Commercial data

Packaging size	2
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140521629
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC001855
UNSPSC 24.0	26121604