




NOTES, UNLESS OTHERWISE SPECIFIED:

PART MUST BE RoHS COMPLIANT.

1. DIMENSIONS IN BRACKETS ARE IN METRIC.
2. RECOMMENDED TOOL: CT-3001/ST
3. COMPATIBLE TOOLS: CT-2931/ST, CT-920CH, CT-930LPCH
4. WIRE SIZE: 350kcm²
5. CRIMPS: F93 FERRULES - ALL SIZES
6. DIE HALVES ARE HEAT TREATED TO Rc 32-35
7. DIE HALVES ARE NICKLON PLATED FOR LUBRICITY/DURABILITY

B



INSTALLATION INSTRUCTION NUMBER PA28870A01					FMEA & CONTROL PLAN NUMBER N/A						
TITLE CD-920-F93 CUSTOMER DRAWING											
CUSTOMER DRAWING											
ITEM REVISION NAME R28879AA/00											
DATASET FILE NAME R28879AA-00-dwg1											
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]											
.x ± .1 [2.54] .xx ± .01 [.25]				.xxx ± .005 [.127] ANGLES ± 5 °							
THIRD ANGLE PROJECTION											
MATERIAL: 4140 STEEL / RC 32-35											
DRAWING NUMBER: TD28879A01											
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY BJPU	DATE 03/30/17	CHK JADE	SCALE 1:1	SIZE A
00	03-30-17	BJPU	JEH	JADE	RELEASED	012679					