



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	MAX BUNDLE DIAMETER	PACKAGE QTY	LENGTH ('L") +/- .3" [7]
IMLTFC38H-C6L	1.5" [38]	100	6.2" [158]
IMLTFC51H-L6L	2" [51]	50	7.9" [201]
IMLTFC64H-C6L	2.5" [64]	100	9.4" [233]
IMLTFC69H-L6L	2.7" [69]	50	10.2" [259]
IMLTFC86H-C6L	3.4" [86]	100	12.2" [310]
IMLTFC102H-L6L	4" [102]	50	14.3" [362]
IMLTFC137H-C6L	5.4" [137]	100	18.2" [462]
IMLTFC152H-L6L	6" [152]	50	20.5" [521]
IMLTFC203H-L6L	8" [203]	50	26.8" [679]



- NOTES:
1. APPLICATION TOOLS - GS4MT,PPTMT,ST2MT,HTMT,PBTMT
 2. MINIMUM LOOP TENSILE STRENGTH - 200 LBS. (890 NEWTONS) WHEN TESTED ON A 1.5" MANDREL.
 3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
 4. TOLERANCES:
.XXX = ±.010 [.25] .XX = ±.02 [.5]
.X = ±.03 [.8] ANGLES = ±2°
 5. MATERIAL: 316L STAINLESS STEEL
 6. COATING - EPOXY POLYESTER



TITLE	
IMLT HEAVY FULLY COATED SINGLE LOOP ASSEMBLY 316L STAINLESS STEEL	
CONTROL DRAWING	
ITEM REVISION NAME	
15L355BG/00	
DATASET FILE NAME	
15L355BG_DC/00	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °	
THIRD ANGLE PROJECTION	
DRAWN BY	
JSUN	
DATE	
3-7-16	
CHK	
JSUN	
SCALE	
2:1	
MATERIAL:	
316L STAINLESS STEEL	
DRAWING NUMBER:	
15L355BG_DC	
SHT 1 OF 1	
SIZE	
A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00	3-7-16	JSUN	SKB	RGRO	INITIAL RELEASE	LPECN_15L355BG_DC/00

