



FiberRunner® 6x4 Routing System

specifications

The 6x4 routing system shall be a system of channel, fittings, and brackets designed to segregate, route, and protect fiber optic and high performance copper cabling. Channel and fittings shall be assembled using pre-assembled couplers. A selection of spillout options shall be available that easily attach using the vertical tee. Fittings maintain a minimum 2" bend radius to protect against signal loss due to excessive cable bends. Available system colors shall be yellow and black. A full complement of brackets shall be available for attaching system components to ladder rack, threaded rod, auxiliary framing, strut, equipment racks, cabinets, and raised floor pedestals.



technical information



Dimensions are in inches
(Dimensions in parentheses are metric)

Open channel	Cable	No. of Cables
50% fill capacity: (4" pile up)	1.6mm 2.0mm 3.0mm	3,819 2,444 1,086
Fiber Optic Ribbon		
Interconnect	5.20mm	361
Category 6	6.35mm	242
Category 6A	7.57mm	171
Material:	PVC (Channel), PC/ABS (Fittings)	
Flammability:	94V-0	
Approvals:	UL Listed to 2024 Optical Fiber Cable Routing Assemblies	
CSI Spec Form:	LP-CSISPEC-FR	

key features and benefits

Fastest installations	No bolts need to be tightened and no tools are required when installing the QuikLock™ Coupler; QuikLock™ Couplers and Brackets take less than five seconds to make a mechanically secure connection
Easy to maintain	Hinged channel cover installs easily and fully encloses the channel for cable protection; split hinged channel cover creates radiused 3/4" (19mm) opening for easy access to add or remove cables; the 6x4 hinged and split hinged channel covers will stay open between 30° and 90° to allow cable access even in height restricted areas Split fitting covers allow cable to be laid in without removing the fitting cover; the covers are also designed to prevent cables from coming out of the channel as cable is pulled through
System strength	Hinged channel covers and split fitting covers protect cabling and provide fast and easy access for future cabling moves, adds, and changes Robust system of channel, covers, fittings, and other non-metallic system components, protect cable from physical damage; system includes full range of directional and spillout fittings
Versatility	Multiple spillout options include spill-over fittings and the vertical tee which accepts a three-sided trumpet, transition to corrugated tubing and Panduit® FiberRunner™ System
Cable protection	A minimum 2" bend radius maintained throughout all fittings prevents excessive bends in fiber optic cabling

applications

The FiberRunner® 6x4 Routing System is a system of channel, fittings, and brackets designed to segregate, route, and protect fiber optic and high performance copper cabling. It is suited for data center applications where cable is routed from distribution areas to equipment cabinets or racks. It is used in Telco Central Offices to route fiber optic jumper cables between fiber distribution frames and equipment bays. It can be deployed over the racks or in approved underfloor applications. Channel and fittings are assembled using timesaving Panduit® QuikLock™ Couplers.

A selection of spillout options is available that easily attach using different types of cabling. A full complement of QuikLock™ Brackets is available to attach system components to support structures found in all applications. The FiberRunner® 6x4 Routing System is part of the Panduit® complete fiber distribution system, which includes the FiberRunner® 24x4, 12x4, 4x4, and 2x2 Routing Systems, Wyr-Grid™ Overhead Cable Tray System, cable management, and racks.

PANDUIT®
SPECIFICATION SHEET

Channel and Cover

6x4 channel (6"):	FR6X4**
6x4 hinged cover (6"):	FRHC6**
6x4 split hinged cover (6"):	FRSHC6**
Cable retainer:	FRCR6LBL-X

Fittings, Split Covers, and Spillouts

QuikLock™ Coupler:	FRBC6X4L**
Horizontal right angle:	FRRAGX4L**
Horizontal right angle cover:	FRRASC6L**
Horizontal 45°:	FRH456X4L**
Horizontal 45° cover:	FRH45SC6L**
Horizontal tee:	FRT6X4L**
Horizontal tee cover:	FRTSC6L**
4-way cross:	FRFWC6X4L**
4-way cross cover:	FRFWCSC6L**
End cap:	FREC6X4L**
Inside vertical 90°:	FRIVRA6X4L**
Inside vertical 45°:	FRIV45X4L**
Outside vertical 45°:	FROV45SC6L**
Outside vertical 90°:	FROVRA6X4L
Outside vertical 90° cover:	FROVRASC6L**
6x4 to 4x4 FiberRunner® Reducer Fitting:	FRRF6FR4L**
6x4 to 4x4 FiberRunner® Reducer Fitting Cover:	FRRF6FR4SCL**
6x4 FiberRunner® System to 4x4 Fiber-Duct™ Reducer Fitting:	FRRF64**
Adapter to CommScope 6x4 FiberGuide ¹ :	FRADC6X4L**
Adapter to Tyton 8x4 Lightguide ² :	FRTYT68
Adapter to Warren & Brown 8x4 Lightpaths ³ :	FRWBS68
QuikLock™ Vertical Tee:	FRVT6X4L**
Three-sided vertical tee trumpet spillout:	FTR4X4L**
2-port spillout to 1.5" I.D. corrugated tubing:	FIDT4X4LBL
4x4 hinged duct vertical cable manager kit:	FRHD4KT**
Bend radius control trumpet: Low profile reducer 4x4 to 2x2 for vertical tee:	TRC4HDBL
Spill-over with 2x2 exit:	FRLPR42LBL
Spill-over cover with 2x2 exit for 6x4 system:	FRSPJC2X2L**
2x2 three-sided trumpet:	FTR2X2L**
1-port spillout to 1.5" I.D. corrugated tubing:	FIDT2X2L**
2x2 hinged duct vertical cable manager kit:	FRHD2KT**
2x2 FiberRunner® Bend Radius Control Trumpet:	TRC2HDLBL
Spill-over with 4x4 exit:	FRSPJC4X4L**
Spill-over cover with 4x4 exit for 6x4 system:	FRSPJC46L**
Dual downspout:	FRDDS6X4L**
Dual downspout cover:	FRDDSHC6L**
4x4 three-sided trumpet:	FRT4X4L**
2-port spillout to 1.5" I.D. corrugated tubing:	FRIDT4X4L**
Three-sided BRC trumpet spillout for 6x4 exit:	FRTR6X4L**
6x4 up spout:	FRUPS6X4L**
Innerduct transition fitting:	FITF6X4
Corrugated tubing spillout:	FRIDT6X4L**
QuikLock™ Mounting Brackets	
QL existing 1/2" thr rod bracket:	FR6TRBE12
QL existing 5/8" thr rod bracket:	FR6TRBE58
QL new 1/2" thr rod bracket:	FR6TRBN12
QL new 5/8" thr rod bracket:	FR6TRBN58
QL underfloor bracket:	FR6USB
QL adjust ladder rack bracket:	FR6ALB
QL center support bracket 1/2":	FR6CS12
QL center support bracket 5/8":	FR6CS58
QL adjust C-bracket 1/2":	FR6ACB12
QL adjust C-bracket 5/8":	FR6ACB58
QL trapeze 3/8" bracket:	FR6TB38
QL trapeze 1/2" bracket:	FR6TB12
Two-piece ladder rack bracket 1/2" thr rod:	F2PCLB12
Two-piece ladder rack bracket 5/8" thr rod:	F2PCLB58
QL ladder rack bracket:	FR6LRB
QL "L" wall mount bracket:	FR6LB
QL NetFrame™ Rack Mount Bracket:	FRRMBNF58
QL adjust cabinet mount bracket:	FR6ACAB
Two-piece framing clip 5/8" thr rod to 9/16" C-channel aux. framing bars:	FRAFC58
4 post rack bracket:	FR4PRB58

¹ FiberGuide is a registered trademark of CommScope Telecommunications, Inc.

² Lightguide Fiber Optic Protection System is a product of the Hellerman Tyton Corporation

³ Lightpath is a trademark of Warren & Brown Technologies Ltd.

** Substitute: YL= Yellow, BL= Black


FiberRunner® 6x4 Routing System

channel and cover




FR6X4**6 FRHC6**6 FRSHC6**6

fittings, split covers, and spillouts



QuikLock™ Mounting Brackets



**Substitute: YL = Yellow, B = Black

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

© 2020 Panduit Corp.
ALL RIGHTS RESERVED.
FRSP30-WW-ENG
10/2020

PANDUIT®