

M12 X-cod st/st m/m PUR 5.0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 33 050 5810 050
Specification	M12 X-cod st/st m/m PUR 5.0m
HARTING eCatalogue	https://harting.com/21330505810050

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 X-coding Male Straight Press&Go
Connector 2	M12 X-coding Male Straight Press&Go
Type of cable	Copper cable (round)

Version

Cable length	5 m
Number of cores	8
Core structure	4x 2x AWG 26/7
Shielding	Shielded
Coding	X-coding

Technical characteristics

Transmission characteristics	Cat. 6A Class EA up to 500 MHz
------------------------------	--------------------------------

Technical characteristics

	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Data rate	
Limiting temperature	-40 ... +80 °C moved -40 ... +80 °C unmoved
Cable diameter	6.7 mm ± 0.3 mm

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Yellow
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	567c8b78-5fa0-43aa-a4c0-beb9d99b7769
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	UN/ECE-R 118 fire protection for rolling stock
----------------	--

Commercial data

Packaging size	1
Net weight	300 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140248700
eCl@ss	27060390 Ready-made data cable (unspecified)

Commercial data

ETIM	EC002599
UNSPSC 24.0	26121600