


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. ** (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT1M-71	.06 (1.5)	.87 (22)	.048 (1.2)	.101 (2.6)	.192 (4.9)	.130 (3.3)	.190 (4.8)	4.00 (101.6)	35 (156)	MINIATURE	CURVED	.08 (36)
PLT1.5M-71	.06 (1.5)	1.38 (35)	.048 (1.2)	.101 (2.6)	.192 (4.9)	.130 (3.3)	.190 (4.8)	5.90 (149.9)	35 (156)	MINIATURE	CURVED	.11 (52)
PLT2S-71	.13 (3.3)	1.88 (48)	.055 (1.4)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	7.40 (188)	150 (668)	STANDARD	STRAIGHT	.38 (173)

NOTES :

- *1) SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL AND PART COLOR
- 2) MATERIAL HAS A UL RELATIVE THERMAL INDEX RATING OF 464°F (240°C).
- 4) EXCELLENT RESISTANCE TO MOST CHEMICALS.
- **5) MINIMUM LOOP TENSILE RATING AT 73°F (23°C).

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

							TITLE PREMIUM CABLE TIES PLT ELEVATED TEMPERATURE SERIES CUSTOMER DRAWING						
							ITEM REVISION NAME W10035DS/05				PANDUIT		
							DATASET FILE NAME W10035DS_DC/08A						
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .1 (2.5) .XXX ± .020 (.51) .XX ± .02 (.5) ANGLES ± _____ THIRD ANGLE PROJECTION				MATERIAL: PEEK - COLOR:BROWN REG. T.M. OF VICTREX MFG. LTD		
											DRAWING NUMBER: W10035DS_DC		
08A	10.03.24	BWG	JADE	DJSL	UPDATED TITLE BLOCK WITH ALTERNATE DESCRIPTION	005806/00							
07	3/23/23	BWG	DAEI	DJSL	E. REVISED NOTE 1. D. UPDATED DRAWING NUMBER C. REMOVED NOTE 3. B. REVISED NOTE 2. A. UPDATED TITLE BORDER TO LATEST FORMAT.	129922/00							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY JABO	DATE 06/01/04	CHK DM	SCALE NONE	SHT 1 OF 1	SIZE A	