

# TX6™ PLUS 30 AWG UTP Modular Plug

**PANDUIT®**  
SPECIFICATION SHEET

## SPECIFICATIONS

Category 6/Class E, 8-position, 8-wire, UTP modular plug shall terminate most 4-pair, 30 AWG, 100 ohms, stranded, unshielded twisted pair cable with maximum conductor insulation diameter of 0.021 inch (0.53mm). Pair manager simplifies termination and provides strain relief for small diameter 30 AWG cable. Modular plug shall terminate to T568A and T568B wiring schemes.



## TECHNICAL INFORMATION

<b>ANSI/TIA and ISO compliance:</b>	Meets TIA/EIA Category 6 and ISO Class E performance requirements for NEXT and RL when properly terminated to category compliant cable
<b>IEC compliance:</b>	IEC 60603-7
<b>c(UL) listed:</b>	UL 1863, CSA Standard C22.2
<b>Conductor termination:</b>	Compatible with most 30 AWG stranded cables with 0.122 in.-0.130 in. (3.10mm - 3.30mm) outer jacket diameter and 0.021 in. (0.53mm) maximum conductor insulation diameter
<b>RoHS compliance:</b>	Compliant
<b>Plug housing:</b>	UL94V-0 rated clear Polycarbonate
<b>Cable manager:</b>	UL94V-0 rated clear, tinted Polycarbonate
<b>Contacts:</b>	Gold plated phosphor bronze
<b>Operating temperature:</b>	14°F to 140°F (-15°C to 60°C)
<b>Storage temperature:</b>	-40°F to 158°F (-40°C to 70°C)

## KEY FEATURES AND BENEFITS

<b>Patented tangle-free latch:</b>	Prevents snags and provides easy release, saving time and providing reliability on frequent moves, adds, and changes
<b>Robust construction:</b>	Rated to 2500 mating cycles

## APPLICATIONS

Category 6 plugs allow customers to meet performance requirements in ISO 11801 Class E, IEEE 802.3an-2006 and ANSI/TIA-568-C.2 Category 6 Standards to support transmission at speeds up to and including 1000BASE-T. These plugs can be used in applications such as high-performance workstations, 155 Mb/s ATM, 622 Mb/s ATM, 1.2 Gb/s ATM, Token Ring 4/16, digital video and broadband/baseband analog video, and Voice over IP.

## TX6 PLUS 30 AWG UTP Modular Plug

**TG-Style module (100 pieces):** SP630-C

### Tools and Accessories


<b>Small gauge plug assembly tool:</b>	SGPT
<b>Crimp tool:</b>	MPT5-8AS
<b>RJ45 plug lock-in device (standard):</b>	PSL-DCPLE**+
<b>RJ45 plug lock-in device (recessed):</b>	PSL-DCPLRE**+

\*\*Colors other than Red: -BL (Black), -BU (Blue), -GR (Green), -YL (Yellow), -OR (Orange), -IW (International White), or -IG (International Gray)

+Add -X for packages of 10 or -C for packages of 100 packages of 100

# TX6™ PLUS 30 AWG UTP Modular Plug

## ENGINEERING DRAWINGS



Dimensions are in inches. [Dimensions in brackets are metric].

---

### WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Guadalajara, Mexico  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

For more information

Visit us at [www.panduit.com](http://www.panduit.com)  
Contact Customer Service by email: [cs@panduit.com](mailto:cs@panduit.com)  
or by phone: 800.777.3300

**PANDUIT**®

© 2024 Panduit Corp.  
ALL RIGHTS RESERVED.  
COSP296-WW-ENG  
7/2024