

SPECIFICATION

- STANDARD:
 CABLE TYPE: UL3512 200°C 600V
 CABLE DIAMETER: 3-CORE $\phi 17$ /1-CORE $\phi 8$
 6 AWG, 3 CONDUCTORS
 USE WITH UPS CAPACITY: 5/6/10kVA
 WORKMANSHIP STANDARD: HARNESS TO BE MANUFACTURED TO IPC/WHMA-A-620 CLASS 2 STANDARD


- ADDITIONAL:
 NONE

- ACCESSORIES:
 RJ45 COM 5 METER CABLE (1PC)


NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
- 100% TESTING TO BE CARRIED OUT PRIOR TO SHIPPING: MUST BE TESTED FOR CONTINUITY, OPENS, SHORTS & WIRE MAPPING


FRONT VIEW



LEFT VIEW
CONNECTOR COLOR: WHITE



RIGHT VIEW
CONNECTOR COLOR: GREY



PIN	FUNCTION
1	BATTERY +
2	GROUND
3	BATTERY -

IDENTIFICATION/PN TABLE:

PART NUMBER	DESCRIPTION	SHIPPING WEIGHT (KG)
UVPL12HCBL	EBP POWER CABLE & RJ45 COM CABLE 12H 5METER FOR 5, 6, 10kVA LITHIUM SINGLE PHASE UPS	4.7

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	06/13/2024	HQ	JOSD	RRQ/MJD	RELEASE TO PRODUCTION	005385							

PART NAME		BATTERY CABLE	
UVPL12HCBL		UVPL12HCBL	
DRAWN FOR TITLE		UVPL12HCBL	
ALL TOLERANCES ARE ± 0.100 mm UNLESS OTHERWISE SPECIFIED		N/A	
THIRD ANGLE PROJECTION		THIRD ANGLE PROJECTION	
DATE		DATE	
06/13/2024		06/13/2024	
SHEET		SHEET	
1		1	