



SPECIFICATION

- 1. STANDARD:  
 CABLE TYPE: UL2587 90°C 600V  
 CABLE DIAMETER: 3-CORE Ø17.4/1-CORE Ø6.6  
 8 AWG, 3 CONDUCTORS  
 USE WITH UPS CAPACITY: 5/6/10kVA  
 WORKMANSHIP STANDARD: HARNESS TO BE MANUFACTURED TO IPC/WHMA-A-620 CLASS 2 STANDARD
- 2. ADDITIONAL:  
 NONE
- 3. ACCESSORIES:  
 BATTERY TEMPERATURE DETECTION 5 METER CABLE (1PC)


FRONT VIEW



LEFT VIEW  
CONNECTOR COLOR: BLACK



RIGHT VIEW  
CONNECTOR COLOR: BLACK



PIN	FUNCTION
1	BATTERY +
2	BATTERY N
3	BATTERY -

NOTES:

- 1. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
- 2. 100% TESTING TO BE CARRIED OUT PRIOR TO SHIPPING: MUST BE TESTED FOR CONTINUITY, OPENS, SHORTS & WIRE MAPPING

IDENTIFICATION /PN TABLE:

PART NUMBER	DESCRIPTION	SHIPPING WEIGHT (KG)
UVP5T10VCBL	EBP POWER CABLE 240VDC & BATTERY TEMPERATURE DETECTION CABLE 5 METER, FOR 5, 6, 10kVA VRLA SINGLE PHASE UPS	3.7

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DATE	BY	CHK	APR	DESCRIPTION	ECN	DATE	BY	CHK	APR	DESCRIPTION	ECN	
00A	06/13/2024	HQ	JOSD	RRQ/MJD	RELEASE TO PRODUCTION	005385													
001	06/13/2024																		

BATTERY CABLE  
UVP5T10VCBL  
CUSTOMER DRAWING

NEW NUMBER ONLY  
UVP5T10VCBL  
OBSOLETE P/N ONLY  
UVP5T10VCBL

ALL TOLERANCES ARE +/-100mm  
UNLESS OTHERWISE SPECIFIED

THIRD ANGLE PROJECTION

SECRET NUMBER: UVP5T10VCBL-DC

**PANDUIT**

N/A

DATE: 06/13/2024

TIME: 10:00

SCALE: VARIOUS

SHEET: 1 OF 1