


PANDUIT
18900 PANDUIT DRIVE, 60487, USA
WWW.PANDUIT.COM



UNINTERRUPTIBLE POWER SYSTEMS
MODEL NUMBER: U01N14L
INPUT: 100~125 VAC 1 50/60Hz 1 9.4 A Max. 1 1PH+N+PE
BATTERY INPUT: ≤28 V — 45 A
BATTERY CAPACITY/ENERGY: 25.6 V / 9 Ah / 230.4 Wh
OUTPUT: 100/110/115/120/125 VAC 1 50/60Hz 1 1PH+N+PE
1000VA/900W, 8.0A (@125VAC input)
1000VA/900W, 8.4A (@120VAC input)
1000VA/900W, 8.7A (@115VAC input)
1000VA/900W, 9.1A (@110VAC input)
920VA/830W, 9.2A (@100VAC input)
Icc: 3 kA
PROHIBIDO SU USO EN EXTERIORES
MADE IN xxx
HECHO EN xxx



LEGEND			
SYMBOL	DESCRIPTION	SYMBOL	DESCRIPTION
	CIRCUIT BREAKER		AC-DC CONVERTER
	RELAY		DC-AC CONVERTER (INVERTER)
	DC-DC CONVERTER		AC-DC CHARGE
			BATTERY

				TYPE			
				UPS			
				U01S14L/U01N14L			
				CUSTOMER DRAWING			
				PART NUMBER NAME			
				U01S14L/U01N14L/00			
				BATTERY NAME			
				U01S14L/U01N14L-DC/00A			
				UNLESS OTHERWISE SPECIFIED			
				DIMENSIONAL TOLERANCES AND FIT (IN)			
				N/A			
				THIRD ANGLE PROJECTION			
				U01N14L-DC			
				SHT 2 OF 2			