

# US-EMLP (40X10) SR CUS - Plastic label

0830367

<https://www.phoenixcontact.com/us/products/0830367>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic label, Card, can be ordered: by card, silver, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 28, text field height: 10 mm, text field width: 40 mm



## Your advantages

- All US-EMLP ... device markers can also be supplied labeled according to customer requirements
- PVC material flammability rating V0 in accordance with UL 94

## Commercial data

Item number	0830367
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8149
Catalog page	Page 261 (C-5-2013)
GTIN	4046356723510
Weight per piece (including packing)	18.44 g
Weight per piece (excluding packing)	18.44 g
Country of origin	PL

# US-EMLP (40X10) SR CUS - Plastic label

0830367

<https://www.phoenixcontact.com/us/products/0830367>



## Technical data

### Product properties

Product type	Labeled device marker
Marking	
Number of individual labels	28
Number of individual labels per row	2
Identification technology	Thermal transfer for sheets and cards

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

Result	Test passed
Test for substances that would hinder coating with paint or varnish	

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

### Mounting

Mounting type	adhesive
Mounting type	

### Material specifications

RoHS compliant	yes
Foil strength	500 µm
Adhesive strength	50 µm
Adhesive	Acrylic
Color	silver
Material	PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

Result	Test passed
Test for substances that would hinder coating with paint or varnish	

#### UV resistance

# US-EMLP (40X10) SR CUS - Plastic label

0830367

<https://www.phoenixcontact.com/us/products/0830367>



Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

## Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

## Dimensions

Width	40 mm
Length	10 mm

## Text field

Text field width	40 mm
Text field height	10 mm

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

# US-EMLP (40X10) SR CUS - Plastic label

0830367

<https://www.phoenixcontact.com/us/products/0830367>



## Classifications

### ECLASS

ECLASS-13.0	27281103
-------------	----------

### ETIM

ETIM 9.0	EC001288
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# US-EMLP (40X10) SR CUS - Plastic label

0830367

<https://www.phoenixcontact.com/us/products/0830367>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)