

UT 6-TMC M 12A - Thermal-magnetic device circuit breaker



0916611

<https://www.phoenixcontact.com/us/products/0916611>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Thermal-magnetic circuit breaker, 1-pos., for DIN rail mounting



Your advantages

- Simple feed-in due to bridging capability using CLIPLINE complete accessories
- High system availability, thanks to easy resetting
- Quick and easy identification with large-area marking options
- The right device for every application, thanks to a nominal current range of 0.5 to 16 A
- Space savings of 30 % compared to miniature circuit breakers owing to the compact width of 12.3 mm

Commercial data

Item number	0916611
Packing unit	6 pc
Minimum order quantity	6 pc
Sales key	CL16
Product key	CLA122
Catalog page	Page 394 (C-4-2019)
GTIN	4046356449472
Weight per piece (including packing)	64.51 g
Weight per piece (excluding packing)	64.51 g
Customs tariff number	85362010
Country of origin	CZ

UT 6-TMC M 12A - Thermal-magnetic device circuit breaker



0916611

<https://www.phoenixcontact.com/us/products/0916611>

Technical data

Product properties

Product type	Thermomagnetic device circuit breakers
Product family	UT 6-TMC
Type	DIN rail module, one-piece
Number of positions	1
Number of connections	2
Number of rows	1
No. of channels	1
Potentials	1

Insulation characteristics

Overvoltage category	II
Degree of pollution	2

Electrical properties

Fuse type	Automatic device
Maximum power dissipation for nominal condition	$\leq 1.57 \text{ VA}$

General

Operating voltage	50 V AC ... 264 V AC (48 - 62 Hz)
	5 V DC ... 30.8 V DC
Rated voltage	240 V AC (50/60 Hz)
	28 V DC
	240 V AC (50/60 Hz)
	28 V DC
Rated insulation voltage U_i	440 V AC
Rated current I_N	12 A
Rated surge voltage	2.8 kV
Insulation resistance R_{iso}	$> 100 \text{ M}\Omega$ (main contact)
Type of actuation	S type
Tripping method	TM (thermal-magnetic)
Tripping level	Trip-free mechanism (positive)
Device resistance	10.9 m Ω
Required backup fuse	25 A
Rated short-circuit switching capacity I_{cn}	200 A (240 V AC)
	400 A (28 V DC)
Dielectric strength	2000 V
Switching cycles, max.	6000 (at $1 \times I_n$)
	50 (at $1.5 \times I_n$)
	40 (at $6 \times I_n$)
Fuse	M1 (normal blow)
Power dissipation	$\leq 1.57 \text{ VA}$

UT 6-TMC M 12A - Thermal-magnetic device circuit breaker



0916611

<https://www.phoenixcontact.com/us/products/0916611>

Temperature derating	9.24 A DC (at -30 °C)
	9.6 A DC (at -20 °C)
	10.2 A DC (at -10 °C)
	10.8 A DC (at 0 °C)
	11.4 A DC (at 10 °C)
	12 A DC (at 23 °C)
	12.36 A DC (at 30 °C)
	12.96 A DC (at 40 °C)
	13.8 A DC (at 50 °C)
	14.52 A DC (at 60 °C)
Contact switching type	none

Indicator/remote signaling

Connection name	Auxiliary contact
-----------------	-------------------

Connection data

Nominal cross section	6.00 mm²
Rated cross section AWG	8
Connection method	Screw connection

Level 1 above 1 below 1

Screw thread	M4
Tightening torque	1.5 ... 1.8 Nm
Stripping length	12 mm
Conductor cross section rigid	0.2 mm² ... 10 mm²
Cross section AWG	24 ... 8 (converted acc. to IEC)
Conductor cross section flexible	0.2 mm² ... 10 mm²
Conductor cross section, flexible [AWG]	24 ... 8 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.25 mm² ... 6 mm²
Flexible conductor cross section (ferrule with plastic sleeve)	0.25 mm² ... 6 mm²
2 conductors with same cross section, solid	0.2 mm² ... 2.5 mm²
2 conductors with same cross section, flexible	0.2 mm² ... 2.5 mm²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.25 mm² ... 1.5 mm²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm² ... 4 mm²
Nominal current	12 A
Nominal voltage	240 V AC
	28 V DC
Nominal cross section	6 mm²

Main contact

Connection method	Screw connection
Screw thread	M4
Tightening torque	1.5 Nm ... 1.8 Nm
Stripping length	12 mm

UT 6-TMC M 12A - Thermal-magnetic device circuit breaker



0916611

<https://www.phoenixcontact.com/us/products/0916611>

Conductor cross section flexible	0.2 mm² ... 10 mm²
Conductor cross section rigid	0.2 mm² ... 10 mm²
Conductor cross section AWG	24 ... 8
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm² ... 4 mm²
Conductor cross section, flexible, with ferrule, with plastic sleeve	0.25 mm² ... 6 mm²
Conductor cross section flexible, with ferrule without plastic sleeve	0.25 mm² ... 6 mm²

Dimensions

Width	12.3 mm
Height	85.5 mm
Depth	89.5 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V-0
Insulating material	PA66

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP40 (Actuation area)
	IP20 (Connection area)
Ambient temperature (operation)	-30 °C ... 60 °C
Altitude	2000 m (acc. to EN 60934)

Standards and regulations

Standards/specifications	EN 60934
Standards/specifications	UL 1077
Standards/specifications	CSA 22.2
Note	No. 235
Standards/specifications	EAC

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------


UT 6-TMC M 12A - Thermal-magnetic device circuit breaker

0916611


<https://www.phoenixcontact.com/us/products/0916611>

Drawings

Application drawing



Application drawing



UT 6-TMC M 12A - Thermal-magnetic device circuit breaker

0916611


<https://www.phoenixcontact.com/us/products/0916611>

Diagram



Trigger characteristic

Block diagram



UT 6-TMC M 12A - Thermal-magnetic device circuit breaker



0916611

<https://www.phoenixcontact.com/us/products/0916611>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0916611>



cUL Recognized
Approval ID: FILE E 140459



UL Recognized
Approval ID: FILE E 140459



EAC
Approval ID: EAC-Zulassung



EAC
Approval ID: RU C-DE.A*30.B01546



VDE approval of drawings
Approval ID: 40028127



CSA
Approval ID: 250505



KC
Approval ID: SW05013-15001

UT 6-TMC M 12A - Thermal-magnetic device circuit breaker



0916611
<https://www.phoenixcontact.com/us/products/0916611>

Classifications

ECLASS

ECLASS-13.0	27140401
-------------	----------

ETIM

ETIM 9.0	EC003538
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UT 6-TMC M 12A - Thermal-magnetic device circuit breaker



0916611

<https://www.phoenixcontact.com/us/products/0916611>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	9ca93b1d-47b5-4d8b-8b79-74566344ad20

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com